

CABINET TRANSFORMATIONS™ DECORATIVE GLAZE

DESCRIPTION AND USES

Cabinet Transformations[™] is a process designed to refinish your worn or damaged cabinets with a four step coating system. Cabinet Transformations is suitable for kitchen and bathroom, or any other cabinet in your home.

Cabinet Transformations uses a system of an adhesive bond coat, decorative glaze (optional), and a protective clear top coat to create a highly durable finish.

The Cabinet Transformations kit includes both an instructional DVD and printed instructions to aid with the process and coating application. The kit also includes:

- Deglosser
- Bond Coat
- · Decorative Glaze
- Protective Top Coat
- · Decorative Glazing Cloths
- Scrub Pads
- · Stir Sticks

Items not supplied with the kit which need to be purchased separately:

- (3) 2" Synthetic Paint Brushes Premium Quality
- (1) 2" Foam Paint Brush (for optional glaze)
- Smooth Painter's Tape (2" size)
- Drop Cloths
- Plastic Sheeting
- Disposable Gloves
- Lint-Free Rags
- Disposable Paint Containers

Suggested Items Needed:

- Screwdriver or Cordless Screwdriver
- Plastic Wood Filler and Putty Knife (if filling hardware holes)
- · Plastic or Cork Bumpers
- Plastic Cups or Baggies (for hardware)
- Sketch Paper and Marker

PRODUCTS

SKU Description

226227 1-Quart Decorative Glaze

PRODUCT APPLICATION

Watch the entire instructional DVD and use the printed instructions for the complete, step by step, procedure on application of the materials.

IMPORTANT: Apply when air (ambient) temperature is 50-95°F (10-35°C) and relative humidity is below 60%.

PRODUCT APPLICATION

SURFACE PREPARATION

To obtain best results, take cabinet doors off hinges and drawers out of frames. Remove all cabinet hardware, including hinges, drawer pulls, and knobs. The surface of the cabinets must be completely cleaned and de-glossed in accordance to the instructions to ensure proper performance of the Cabinet Transformations.

APPLICATION OF DEGLOSSER

To ensure optimum results and maximum adhesion of the Bond Coat, make sure to be THOROUGH in deglossing the cabinet doors, drawers, and frames. **IMPORTANT:** When deglossing wooden cabinetry, follow the grain pattern of the wood. Avoid scrubbing in a circular motion. Wipe up any spilled Deglosser with a clean cloth.

APPLICATION OF BOND COAT

The Bond Coat is formulated to provide maximum adhesion to wood, laminate, and melamine surfaces. Two coats of Bond Coat are recommended. Allow the final coat of Bond Coat to dry at least 2 hours before applying the Decorative Glaze. **IMPORTANT**: There is enough Bond Coat to cover the outer cabinet frame, each drawer front, and front and back of each door with two coats. There is not enough to coat the insides of the cabinets or shelves. See instructional pamphlet for additional glazing techniques.

APPLICATION OF DECORATIVE GLAZE (optional)

The Decorative Glaze enhances the look of the cabinets by accenting the Bond Coat color giving a high-end, custom look. Thoroughly stir the Decorative Glaze using a stir stick. Working in cabinet door, drawer or frame sections; use a 2" synthetic brush or 2" foam brush to liberally coat the surface with Decorative Glaze. Be sure to coat all corners, crevices, and raised panel sections. Using the Decorative Glazing Cloths, wipe the surface in the direction of the grain to remove the glaze to your desired look. If dissatisfied, while wet, wipe completely clean with a damp cloth and repeat the glazing process. Allow the Decorative Glaze to dry for a minimum of 8 hours before applying the Protective Top Coat.

NOTE: Decorative Glaze will be very subtle over dark Bond coat colors.

APPLICATION OF THE TOPCOAT

1

The topcoat is formulated with self cross-linking technology that provides superior stain and scratch resistance. **IMPORTANT:** The Protective Top Coat dries quickly. For best results, avoid re-brushing previously coated areas that have started to dry.

Allow to dry 12 hours before installing cabinet drawers and hardware. Allow 24 hours before full use. Avoid using cleaners on new cabinetry for 7 days.

Form: GDH-44 Rev.: 041017





CABINET TRANSFORMATIONS™ DECORATIVE GLAZE

PHYSICAL PROPERTIES

			DECORATIVE GLAZE
Resin Type			Acrylic
Pigment Type			None
Solvents			Propylene Glycol
Weight	Per Gallon		8.67 lbs.
	Per Liter		1.04 kg
Volatile Organic Compounds			856 g/l (7.12 lbs./gal.)
Practical Coverage at Recommended DFT (assumes 15% material loss)			NA
(21-27°C) and 50% Relative Humidity		Allow Bond Coat to Dry	2 hours
		Allow Decorative Glaze to Dry	8 hours
Shelf Life			3 years
Flash Point			>200°F (93°C)
Safety Information			For additional information, see SDS

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Phone: 877•385•8155 www.rustoleum.com Form: GDH-44 Rev.: 041017